





PRODUCT CONFORMITY CERTIFICATE

This is to certify that the

ISCO 5800 Automatic Waste Water Sampler

manufactured by:

Teledyne ISCO

4700 Superior Street Lincoln Nebraska NE 68504 USA

has been assessed by Sira Certification Service and for the conditions stated on this certificate complies with:

MCERTS Performance Standards for Continuous Water Monitoring Equipment, Version 2.1 (November 2009)

Certification Range :

Lift height 0 to 7 metres

Project No: Certificate No: Initial Certification: This Certificate Issued Renewal Date: 16W29523 Sira MC 130227/00 10 July 2013 10 July 2013 09 July 2018

Technical Director

MCERTS is operated on behalf of the Environment Agency by

Sira Certification Service

12 Acorn Industrial Park, Crayford Road, Crayford Dartford, Kent, UK DA1 4AL Tel: +44 (0)1322 520500 Fax: +44 (0)1322 520501

This certificate may only be reproduced in its entirety and without change To authenticate the validity of this certificate please visit www.siracertification.com/mcerts **Registered Office:** Rake Lane, Eccleston, Chester, UK CH4 9JN









Approved Site Application

The product is suitable for use on applications for compliance with the Urban Wastewater Treatment Regulations.

Any potential user should ensure, in consultation with the manufacturer, that the emission monitoring system is suitable for the process on which it will be installed.

Basis of Certification

This certification is based on the following Test Report(s) and on Sira's assessment and ongoing surveillance of the product and the manufacturing process:

| WRc report | Report Reference: UC 7399 dated May 2007 |
|------------|--|
| WRc report | Report Reference: UC 9502 dated March 2013 |

Product Certified

The 5800 automatic wastewater sampler consists of the following parts:

- 5800 control panel
- 5800 pump assembly
- 5800 distributor assembly
- 5800 refrigeration system

This certificate applies to all instruments fitted with software version 1.00.0006 onwards (serial number 213A00001 onwards).







Certified Performance

The instrument was evaluated for use under the following conditions:

-10°C to +40°C Ambient Temperature Range:

| Test | Results | | MCERTS specification |
|--|---|--|--|
| Sample Collection | Flow proportional and timed sam Certified for use with single 10 lit bottle and 24 X 1 litre bottles. | Clause 3.1.3 | |
| Sample interval | Sample interval range is 1 min to with increments of 1 min is select 4-20mA and pulse outputs are av 1min to 9,999 flow pulses with in | Clause 3.1.4 & 3.1.5 | |
| Sample failure | Sample failures are recorded. Fat | Clause 3.1.6 & 3.1.7 | |
| Sample line diameter | 9.52 mm. | Clause 3.1.8 >9mm | |
| Sample volume | Sample volume adjustable over t in 1ml increments | Clause 3.1.9 | |
| Maximum volume of a discrete sample that can be set Total storage capacity both by numbers and volumes of individual bottles and in a composite container | 9,990ml The following are available: 24 X 1 L PP or 350ml glass 4 X 10 L PE or glass 2 X 10 L PE or glass 1 X 20 L PE or glass 1 X 10 L PE or glass 24 X ProPak, 1 L wedge 1 X ProPak, 10 L round | | Clause 3.2.1 |
| Maximum sampling head | 7 metres | | Clause 3.2.2 |
| Sample volume error – Time proportional | Systematic Errors: 2.03% at 1m 3.29% at 3.5m 4.11% at 7m Overall: 3.14% | Random Errors: 2.69% at 1m -2.46% at 3.5m -4.37% at 7m Overall: -1.38% | Clause 6.2.1a) <5% <5% <5% <5% |

Certificate No: This Certificate Issued: Sira MC 130227/00 10 July 2013 This certificate may only be reproduced in its entirety and without change To authenticate the validity of this certificate please visit www.siracertification.com/mcerts







| Test | Results | | MCERTS specification |
|---|--|----------------------------|-------------------------|
| Sample volume – Constant volume variable time (CVVT) flow proportional sampling | Systematic Errors: | Random Errors: | Clause 6.2.1 b) |
| | 1.77% at 1m | -0.04% at 1m | <5% |
| | 2.41% at 3.5m | -3.89% at 3.5m | <5% |
| | 2.26% at 7m | -2.34% at 7m | <5% |
| | Overall: 2.15% | Overall: -2.09% | <5% |
| Sample volume – Contact time variable volume (CTVV) flow proportional sampling | Systematic Errors: | Random Errors: | Clause 6.2.1 c) |
| | 2.46% at 1m | -0.03% at 1m | <5% |
| | 1.69% at 3.5m | -1.05% at 3.5m | <5% |
| | 1.31% at 7m | 0.71% at 7m | <5% |
| | Overall: 1.83% | Overall: -0.12% | <5% |
| Sample line velocity | | | Clause 6.2.2 |
| | 0.95 m/s at 1m sampling head | | >0.5 m/s |
| | 0.94 m/s at 2m sampling head | | >0.5 m/s |
| | 0.90 m/s at 3m sampling head | | >0.5 m/s |
| | 0.88 m/s at 4m sampling head | | >0.5 m/s |
| | 0.85 m/s at 5m sampling head | | >0.5 m/s |
| | 0.83 m/s at 6m sampling head | | >0.5 m/s |
| | 0.75 m/s at 7m sampling head | | >0.5 m/s |
| Sample integrity | No statistically significant difference was found in analysis for BOD, COD, suspended solids, total N and total P | | Clause 6.2.3 |
| Sample timing | | | Clause 6.2.4 |
| | 4 seconds | | < ±10 sec/24h |
| Ambient temperature effects | Systematic Errors: | Random Errors: | Clause 6.2.5 a) |
| Sampler without sample temperature control | 2.43% at –10°C | 1.43% at -10°C | <5% |
| | 2.58% at 40°C | 3.04% at 40°C | <5% |
| Ambient temperature | During sample period: | 24hrs after sample period: | Clause 6.2.5 b) |
| Sampler with sample | 4.1°C at –10°C | 3.0°C at –10°C | Maintain sample |
| temperature control | 4.3°C at 20°C | 3.8°C at 20°C | between |
| | 4.0°C at 40°C | 3.7°C at 40°C | 0°C to 5°C |







Description:

The 5800 Refrigerated Sampler System consists of a 5800 Control Panel, 5800 Pump Assembly, 5800 Distributor Assembly, and 5800 Refrigeration System.

The 5800 Control Panel provides user programmable sampler features via a keypad and display. The 5800 Pump Assembly consists of a peristaltic pump for pulling samples to the sampler. The 5800 Distributor Assembly distributes the pumped sample into container(s) located in the refrigerator. The sample is transported by 3/8 inch I.D. PVC or PTFE lined suction line.

The refrigeration system utilizes a 1/4 hp compressor running on R134a refrigerant and is controlled by the microprocessor located in the 5800 Sampler Control Panel. The refrigerator cabinet is constructed from UV resistant LLDPE. The refrigeration system constructed from stainless steel and is powered by 230Vac 50 Hz.

General Notes

- 1. This certificate is based upon the equipment tested. The Manufacturer is responsible for ensuring that on-going production complies with the standard(s) and performance criteria defined in this Certificate. The Manufacturer is required to maintain an approved quality management system controlling the manufacture of the certified product. Both the product and the quality management system shall be subject to regular surveillance according to 'Regulations Applicable to the Holders of Sira Certificates'. The design of the product certified is defined in the Sira Design Schedule for certificate No. Sira MC 130227/00.
- 2. If certified product is found not to comply, Sira Certification Service should be notified immediately at the address shown on this certificate.
- 3. The Certification Marks that can be applied to the product or used in publicity material are defined in 'Regulations Applicable to the Holders of Sira Certificates'.
- 4. This document remains the property of Sira and shall be returned when requested by the company.